

PROJECT:

CATALOG #: _____

FIXTURE TYPE:

NOTES:

SALP M1 2.3" Slim Architectural Linear Pendant Mount



The SALP M1 2.3" Slim Architectural Linear Pendant Mount is an ultrasleek lighting solution that is fully customizable to meet the unique needs of each application. The lengths come in 2 ft, 4 ft, and 8 ft with selectable color temperature, wattage, and distributions. The minimalist and elegant aesthetic paired with brilliant illumination and even distribution will elevate your space in a range of applications, including offices, lobbies, and retail spaces. This versatile architectural luminaire possesses unlimited design potential for endless design pattern possibilities.

APPLICATIONS

Commercial, Retail, Hospitality, Education, Airport, Medical, and any open spaces that require a unique and elegant architectural lighting design.



BUILT TO ORDER

All orders are carefully assembled in Houston, TX, to meet the unique needs of each application and project.



Due to continuous product improvements, specification and/or equipment updates may change without notice.


©2023 Spring Lighting Group. All Rights Reserved.



PRODUCT OPTIONS



SELECTABLE LIGHTING DISTRIBUTIONS



CANOPY SIZE & SHAPE



1.6in Round



4.5in Round Designed for power cable

MOUNTING STYLES



Drywall Ceiling w/ Internal Driver



T-Grid Clips Suspends luminaire in T-grid. Compatible with 9/16" and 15/16'' Flat, 9/16" and 15/16" Slot Ceiling Types.



ORDERING GUIDE

The Ordering Guide is not complete without filling out the Layout Sketch located on page 6. If you have any questions, please contact sales.

> ACCESSORIES (Shipped separately. Requires some field assembly.) AVI-XFAC-16A-1CH-CL1 Wireless Circuit Load Controller

EMH 25W 25W Emergency Backup

Luminaire Type	Width	*Length	Lumen Per Ft	Internal Driver	Lens	Generation	ССТ	Finish
SALP 2.3" Width Slim Architectural Linear Pendant Mount	M1 Medium 2.3"	# Total length needed. Increments of 2 feet only.	LS1 500Lm/750Lm/1000lm per ft	CSID Internal Driver with Selectable Distributions 100% up 90% down / 10%up 75% down / 25% up 50% down / 50% up 25% down / 75% up 10% down / 90% up 100% down	F Flat Lens	G1	FSK Field Selectable CCT 3000K/3500K/4000K	Blank White B Black C Custom Color

*Length: The SALP M1 is available in 2', 4', and 8' lengths that can be directly connected together in a continuous run up to 40' (120v) or 100' (277V). Please use the Layout Sketch on page 6 for full details.

MOUNTING

Ceiling Plan	Suspended Lengths
E Dry Wall (Mount to J-box) T1 Drop Ceiling Clips (Suitable for 9/16" and 15/16" Flat Ceiling)	 60 60" Aircraft Cable with 48" Power Cord 144 144" Aircraft Cable with 144" Power Cord 240" Aircraft Cable with 240" Power Cord
 T2 Drop Ceiling Clips (Suitable for 9/16" Slot Ceiling) T3 Drop Ceiling Clips (Suitable for 15/16" Slot Ceiling) 	

PATTERN CONNECTORS

'Y' Ca









· ····································

'l' Connector

1		
or	'Z' Coni	1ecto

Connectors		
X '+' Connector		
T 'T' Connector		
L 'L' Connector		
I 'I' Connector		
Y 'Y' Connector		
Z 'Z' Connector		



SPECIFICATIONS

HOUSING Anodized aluminum extruded body

AMBIENT TEMPERATURE Suitable for use in 0°C to 40°C (32°F to 104°F)

MOUNTING Pendant Mount

EFFICACY Up to 100 Lm/W

ELECTRIC

120V for connections up to 40ft. 277V for connections up to 100ft. Standard 1-10V Dimming. Power factor >0.9, THD <20%. CCT AND CRI Selectable 3000K/3500K/4000K CCT; Standard 80 CRI.

LENS Standard Flat Lens

FINISH Standard White and Black housing in stock. Custom finishes available.


WARRANTY

5-year limited warranty. Please visit www.slgus.com for complete warranty terms.

CERTIFICATIONS

UL Listed for damp location.


DIMENSIONS




Product number	Weight
SALP M14 LS1 CSID F G1 FSK	6.44 lbs
SALP M18 LS1 CSID F G1 FSK	12.46 lbs
SALP M1-C-LC	1 lbs
SALP-DW-WP-KIT	3 lbs
SALP-DW-WP-KIT-T1	3.2 lbs
EMH-25	6.3 lbs



PHOTOMETRIC



AVERAGE ILLUMINANCE CURVE



Note: The Curves indicate the illuminated area and the average illumination when the luminaire is at different distance.

0-5

5-10

10-15

15-20

20-25

25-30

30-35

35-40

40-45

45-50

50-55

55-60

60-65

65-70

70-75

75-80

80-85

85-90

ZONAL LUMEN SUMMARY

∮ zone

20.42

60.56

98.57

133.1

163.1

187.6

205.7

217.0

221.2

218.2

207.9

190.9

167.5

138.6

105.8

71.76

39.81

18.41

 ϕ total

20.42

80.98

179.6

312.7

475.8

663.4

869.1

1086

1307

1525

1733

1924

2092

2230

2336

2408

2448

2466

UNIT[,] Im

%lum,lamp

0.43,0.43

1.71,1.71

3.79,3.79

6.6.6.6

10,10

14,14

18.3,18.3

22.9,22.9

27 6.27 6

32.2,32.2

36.6,36.6

40.6.40.6

44.1,44.1

47.1,47.1

49.3,49.3

50.8,50.8

517,517

52,52

ZONAL FLUX DIAGRAM

Υ CO C45 C90 C135 C180 C225 C270 C315 5 8577 858 1 847 3 841.0 8614 8537 848 1 856 1 10 844.1 849.1 835.1 821.8 851.1 839.3 837.7 851.1 15 822.1 831.6 815.6 795.4 833.5 817.4 819.0 839.8 20 792.8 807 2 788.8 762 5 807.4 788.9 792.8 820.2 25 757.1 755.5 774.6 753.2 775.5 723.0 760.5 793.2 30 716.2 737.2 715.9 677.7 735.6 711.7 721.7 759.2 35 667.9 670.2 627.5 664.2 719.2 693.4 690.3 676.4 616.1 644.0 619.9 572.8 611.7 40 639.9 626.2 673.2 45 559.4 589.1 564.3 513.7 585.0 554.8 571.2 621.7 493.6 50 499 2 530.9 505 0 4513 525.8 5117 565 9 55 434.1 468.3 441.5 385.1 462.7 428.4 448.0 505.6 60 365.3 402.1 374.7 315.6 395.8 360.6 381.1 441.0 65 295 4 9 SEE 305.0 244 5 326.8 310.4 373 2 289.8 70 224.4 260.6 232.0 174.7 254.3 217.5 238.4 302.7 75 154.3 189.1 161.3 108.6 184.1 147.3 166.8 230.2 80 90.07 120 5 95.53 51.77 117.0 99 31 83.82 159.1 85 36.95 41.01 58.12 60.98 10.68 32.86 43.08 93.01 90 39.69 49.44 5.334 21.91 41.89 11.80 5.515 61.74 LUMINOUS INTENSITY:cd DEG


COEFFICIENTS OF UTILIZATION


ррс	80%			70%			50%			30%			10%			0
pw	50%	30%	10%	50%	30%	10%	50%	30%	••••	50%	30%	10%	50%	30%	10%	0
pfc	20%			20%		20%			20%		20%			0		
RCR	RCR:Room Cavlty Ratlo							(CI	J)							
0.0	108	108	108	0	0	0	84	84	84	71	71	71	58	58	58	52
1.0	94	90	86	87	83	80	74	71	69	62	60	58	51	50	48	43
2.0	81	75	70	75	70	65	64	60	57	54	51	48	44	42	40	36
З.О	71	64	58	66	60	54	57	51	47	48	44	41	39	37	34	30
4.0	63	55	49	59	51	46	50	45	40	42	38	32	35	32	29	26
5.0	56	48	42	52	45	39	45	39	35	38	33	30	31	28	25	22
6.0	50	42	36	47	39	34	40	34	30	34	30	26	28	25	22	19
7.0	45	37	32	42	35	30	36	31	26	31	26	23	26	22	20	17
8.0	41	33	28	38	31	26	33	27	23	28	24	20	24	20	18	15
9.0	37	30	25	35	28	23	30	25	21	26	22	18	22	18	16	14
10.0	34	27	22	32	26	21	28	23	19	24	20	17	20	17	14	12



DESIGN PATTERN SAMPLES

CONNECTORS





LAYOUT SKETCH

Layout Sketch Submittal's are required for all custom pattern designs. Please use the grid below for your layout and include all relevant dimensions. Indicate 'Z' connector with a "Z".

									2 ‡

NOTE: Depending on the custom design and desired shape, some configurations may require modifications.

Due to continuous product improvements, specification and/or equipment updates may change without notice.

2 ft